

YCB33R26U

by Burndy
Catalog ID: YCB33R26U

Prop 65 Notice

CRIMPIT™ HOT TAP, 226.8(6-1) kcmil, 336.4(30-7) kcmil, ACSR: 300(37) kcmil, 397.5(19) kcmil Cu or Al



Product Details

General

Die Index	R
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810152799
UPC 12 Digit	7818101527999

Dimensions

Dimension - Bail Size	0.258 in
Dimension - Height inch	2.25 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in

Conductor Related

Conductor - ACSR Str Size	266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	266.8 (26/7) Owl kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Size	300 kcmil;336 kcmil;350 kcmil;397.5 kcmil
Conductor - AL Str Size Range	300 kcmil-397.5 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)