

# YCB35R

by Burndy  
Catalog ID: YCB35R

Prop 65 Notice

Stirrup Connector, Aluminum: 477 kcmil-500 kcmil, ACSR: 397.5(30/7) kcmil-397.5(26/7) kcmil



## Product Details

### General

Die Index	M
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810152782
UPC 12 Digit	7818101527822

### Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5.39 in
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

### Conductor Related

Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil; 397.5 (30/7) Larkspur kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) Ibis kcmil-397.5 (30/7) Larkspur kcmil
Conductor - AL Str Size	477 kcmil; 500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)