

YCB38R26U

by Burndy
Catalog ID: YCB38R26U

Prop 65 Notice

Crimpit Stirrup, 397.5 (19) - 600 (61) Al 336.4 (26-7) - 556.5 (18-1) ACSR, 2-1/8 in L, N Dies.

Features: Combines Figure 6 -Shaped Aluminum CRIMPIT Tap Connector With Tin-Plated Copper Bail, Can Be Gripped In Tool And Slipped Over Line For Easy Installation, Five Sizes Take Range From 4 AWG To 600 MCM, Prefilled With PENETROX Joint Compound And Stripsealed, Bail Size: 1/0 AWG Solid, Conductor Size (run - Range): 336.4 - 600 KCMIL, Conductor Type: Run: ACSR, Aluminum, 6201, 5005, Die Index: N Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-N Die, (2), Y45 Tool, S-N Die, (2), Y46 Tool, P-N Die, (2)



Product Details

General

| | |
|---------------------------|---|
| Application | For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors |
| Die Index | N |
| Material | Aluminum |
| Material - Bail | Copper |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | N |
| Sub Brand | CRIMPIT |
| Trade Name | CRIMPIT™ |
| Type | Stirrups |
| UPC | 781810014110 |
| UPC 12 Digit | 7818100141100 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Bail Size | 0.325 in |
| Dimension - Height inch | 2.28 in |
| Dimension - L Length Overall mm | 54 mm |
| Dimension - Length Overall inch | 2.12 in |

Conductor Related

| | |
|---------------------------------|--|
| Conductor - ACSR Str Size | 336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil |
| Conductor - ACSR Str Size Range | 336.4 (26/7) Linnet kcmil-556.5 (24/7) Parakeet kcmil |
| Conductor - AL Str Size | 397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil |
| Conductor - AL Str Size Range | 397 kcmil-600 kcmil |

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)