

# YCB4U1

by Burndy  
Catalog ID: YCB4U1

Prop 65 Notice

CRIMPIT™ HOT TAP, 4 (6-1) AWG, 4(7-1) AWG, ACSR: 4 AWG Cu or Al



## Product Details

### General

Die Index	D
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810151655
UPC 12 Digit	7818101516555

### Dimensions

Dimension - Bail Size	0.258 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.47 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in

### Conductor Related

Conductor - AAAC 6201 Size	48.69 (7) kcmil
Conductor - ACSR Cmpt Size	4 AWG
Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR Str-Size</li> <li>• AL Str-Size</li> <li>• CU Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	2000
-----------------------	------

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)