

YCHC44TC44

by Burndy
Catalog ID: YCHC44TC44

Prop 65 Notice

Copper Compression C Tap, 1000-750 kcmil (Main), 1000-750 kcmil (Tap),
Tin Plated



Product Details

General

| | |
|----------------|----------------------|
| Color Code | White |
| Connector Type | C-Tap |
| Die Index | 1102 |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | CRIMPIT™ |
| Type | YCHC Series |
| UPC | 781810013748 |
| UPC 12 Digit | 7818100137488 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 3.59 in |
| Dimension - L Length Overall mm | 29 mm |
| Dimension - Length Overall inch | 1.16 in |
| Dimension - Strip Length inch | 1-1/4 |
| Dimension - Width inch | 1.73 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-------------------------------------|----------------------|
| Conductor - Copper Flex I Run Range | 800 kcmil-1000 kcmil |
| Conductor - Copper Flex I Tap Range | 800 kcmil-1000 kcmil |
| Conductor - Copper Flex K Run Range | 800 kcmil-1000 kcmil |
| Conductor - Copper Flex K Tap Range | 800 kcmil-1000 kcmil |
| Conductor - Copper Flex M Run Range | 800 kcmil-1000 kcmil |
| Conductor - Copper Flex M Tap Range | 800 kcmil-1000 kcmil |
| Conductor - Copper Str Run Range | 750 kcmil-1000 kcmil |
| Conductor - Copper Str Tap Range | 750 kcmil-1000 kcmil |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)