

# YCHC8TC8

by Burndy  
Catalog ID: YCHC8TC8

Prop 65 Notice

Cu C-Tap compression connector, # 8-12(8-12)(Main),8-12(8-12)(Tap1), Tin plated, Red, 240 index



## Product Details

### General

Color Code	Red
Connector Type	C-Tap
Die Index	240
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013823
UPC 12 Digit	7818100138233

### Dimensions

Dimension - Height inch	0.53 in
Dimension - L Length Overall mm	13 mm
Dimension - Length Overall inch	0.56 in
Dimension - Strip Length inch	5/8
Dimension - Width inch	0.34 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Run Range	12-8
Conductor - Copper Str Tap Range	12-8

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)