

YCP28L27

by Burndy
Catalog ID: YCP28L27

Prop 65 Notice

Burndy, COPPER / ALUMINUM: 2/0-4/0 AWG,27 IN LANYARD LENGTH,CRIMPS: 2 CRIMPS,ROTATE EA 180 DEG,PAT644, Y644 DIELESS TOOLS.

- Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.

Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.



Product Details

General

Application	Compression pulling grips are single use for pulling electrical cable. The compression pulling head line makes a one-stop-shop for all cable pulling, terminating, splicing, taping, and installation tooling needs
Cable Type	Pull Sleeve
OEM Brand Name	Burndy
Style	Pulling Grips
Sub Brand	COMPRESSION CABLE PULL
Type	YCP
UPC	621945470163

Dimensions

Length	27 in
--------	-------

Conductor Related

Conductor - AL Str Size Range	2/0 - 4/0 AWG
Conductor - Copper Str Size Range	2/0 - 4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)