

## YCP28L34

by Burndy  
Catalog ID: YCP28L34

Prop 65 Notice

Burndy, COPPER / ALUMINUM: 2/0-4/0 AWG, 34 IN LANYARD LENGTH, CRIMPS: 2 CRIMPS, ROTATE EA 180 DEG, PAT644, Y644 DIELESS TOOLS.

- Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.

Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.



## Product Details

### General

Application	Compression pulling grips are single use for pulling electrical cable. The compression pulling head line makes a one-stop-shop for all cable pulling, terminating, splicing, taping, and installation tooling needs
Cable Type	Pull Sleeve
OEM Brand Name	Burndy
Style	Pulling Grips
Sub Brand	COMPRESSION CABLE PULL
Type	YCP
UPC	621945470170

### Dimensions

Length	34 in
--------	-------

### Conductor Related

Conductor - AL Str Size Range	2/0 - 4/0 AWG
Conductor - Copper Str Size Range	2/0 - 4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)