

YCP39L27

by Burndy
Catalog ID: YCP39L27

Prop 65 Notice

Burndy, COPPER / ALUMINUM: 650-750 kcmil, 27 IN LANYARD LENGTH, CRIMPS: 3 CRIMPS, ROTATE EA 180 DEG, PAT644, Y644 DIELESS TOOLS.

- Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.

Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.



Product Details

General

| | |
|----------------|---|
| Application | Compression pulling grips are single use for pulling electrical cable. The compression pulling head line makes a one-stop-shop for all cable pulling, terminating, splicing, taping, and installation tooling needs |
| Cable Type | Pull Sleeve |
| OEM Brand Name | Burndy |
| Style | Pulling Grips |
| Sub Brand | COMPRESSION CABLE PULL |
| Type | YCP |
| UPC | 621945470316 |

Dimensions

| | |
|--------|-------|
| Length | 27 in |
|--------|-------|

Conductor Related

| | |
|-----------------------------------|-----------------|
| Conductor - AL Str Size Range | 651 - 750 KCMIL |
| Conductor - Copper Str Size Range | 651 - 750 KCMIL |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)