

YCR291RG4

by Burndy
Catalog ID: YCR291RG4

Prop 65 Notice

Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR (ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with PENETROX™ and Sealed



Product Details

General

| | |
|---------------------------|---------------|
| Connector Type | Reducer |
| Die Index | 317;705 |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYREDUCER™ |
| UPC | 781810088920 |
| UPC 12 Digit | 7818100889200 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length fraction | 3 in |
| Dimension - B Length inch | 3 in |
| Dimension - L Length Overall mm | 187 mm |
| Dimension - Length BB inch | 3 in |
| Dimension - Length Overall inch | 7.38 in |
| Dimension - Outside Diameter inch | 1.25 in |

Conductor Related

| | |
|-------------------------------------|----------------------------|
| Conductor - ACSR Str Size A | 266.8 (18/1) Waxwing kcmil |
| Conductor - ACSR Str Size A Range | 266.8 (18/1) Waxwing kcmil |
| Conductor - ACSR Str Size B | 4/0 (6/1) Penquin |
| Conductor - ACSR Str Size B Range | 4/0 (6/1) Penquin |
| Conductor - AL Str Size A | 250 kcmil;266.8 kcmil |
| Conductor - AL Str Size A Range | 250 kcmil-266.8 kcmil |
| Conductor - AL Str Size B | 4/0 AWG |
| Conductor - AL Str Size B Range | 4/0 AWG |
| Conductor - Copper Str Size A | 250 kcmil |
| Conductor - Copper Str Size A Range | 250 kcmil |
| Conductor - Copper Str Size B | 4/0 AWG |
| Conductor - Copper Str Size B Range | 4/0 AWG |

| | |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none">• ACSR C Str-Size A• AL C Str-Size A• CU C Str-Size A• ACSR C Str-Size B• AL C Str-Size B• CU C Str-Size B |
|----------------|---|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)