

# YCR32RG5

by Burndy  
Catalog ID: YCR32RG5

Prop 65 Notice

Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR (ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with PENETROX™ and Sealed



## Product Details

### General

Connector Type	Reducer
Die Index	317;705
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYREDUCER™
UPC	781810103968
UPC 12 Digit	7818101039688

### Dimensions

Dimension - B Length inch	3 in
Dimension - L Length Overall mm	170 mm
Dimension - Length BB inch	3 in
Dimension - Length Overall inch	6.69 in
Dimension - Outside Diameter inch	1.25 in

### Conductor Related

Conductor - ACSR Str Size A	336.4 (18/1) Merlin;336.4 (26/7) Linnet
Conductor - ACSR Str Size A Range	336.4 (18/1) Merlin-336.4 (26/7) Linnet
Conductor - ACSR Str Size B	266.8 (18/1) Waxwing
Conductor - ACSR Str Size B Range	266.8 (18/1) Waxwing
Conductor - AL Str Size A	350 kcmil;397.5 kcmil
Conductor - AL Str Size A Range	350 kcmil-397.5 kcmil
Conductor - AL Str Size B	250 kcmil;266.8 kcmil
Conductor - AL Str Size B Range	250 kcmil;266.8 kcmil
Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size A Range	350 kcmil
Conductor - Copper Str Size B	250 kcmil
Conductor - Copper Str Size B Range	250 kcmil

Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size A</li> <li>• AL C Str-Size A</li> <li>• CU C Str-Size A</li> <li>• ACSR C Str-Size B</li> <li>• AL C Str-Size B</li> <li>• CU C Str-Size B</li> </ul>
----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)