

# YCR361RG5

by Burndy  
Catalog ID: YCR361RG5

Prop 65 Notice

Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR (ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with PENETROX™ and Sealed, Acceptable for use on Compact AAC



## Product Details

### General

Connector Type	Reducer
Die Index	317;705
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYREDUCER™
UPC	781810810811
UPC 12 Digit	7818108108111

### Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - L Length Overall mm	187 mm
Dimension - Length BB inch	3 in
Dimension - Length Overall inch	7.38 in
Dimension - Outside Diameter inch	1.25 in

### Conductor Related

Conductor - ACSR Str Size A	397.5 (18/1) Chikkadee;397.5 (26/7) Ibis;477.0 (18/1) Pelican;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size A Range	397.5 (18/1) Chikkadee-477.0 (30/7) Hen
Conductor - ACSR Str Size B	4/0 (6/1) Penguin
Conductor - ACSR Str Size B Range	4/0 (6/1) Penguin
Conductor - AL Str Size A	477 kcmil;500 kcmil
Conductor - AL Str Size A Range	477 kcmil-500 kcmil
Conductor - AL Str Size B	4/0 AWG
Conductor - AL Str Size B Range	4/0 AWG
Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size A Range	500 kcmil
Conductor - Copper Str Size B	4/0 AWG

Conductor - Copper Str Size B Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size A</li> <li>• AL C Str-Size A</li> <li>• CU C Str-Size A</li> <li>• ACSR C Str-Size B</li> <li>• AL C Str-Size B</li> <li>• CU C Str-Size B</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)