


YCS1R

by Burndy
Catalog ID: YCS1R

Prop 65 Notice

Al Compression Loop Splice, #1 AWG ACSR



Product Details

General

Connector Type	Splice
Die Index	241
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810173121
UPC 12 Digit	7818101731211

Dimensions

Dimension - B Length inch	3.12 in
Dimension - L Length Overall mm	162 mm
Dimension - Length Overall inch	6.37 in
Dimension - Outside Diameter inch	0.56 in

Conductor Related

Conductor - ACSR Str Size	1 (6/1) Robin AWG
Conductor - ACSR Str Size Range	1 (6/1) Robin AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	600
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)