

YCS26A

by Burndy
Catalog ID: YCS26A

Prop 65 Notice

Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION),Die Index: 245



Product Details

General

Connector Type	Splice
Die Index	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810820520
UPC 12 Digit	7818108205200

Dimensions

Dimension - B Length inch	2.49 in
Dimension - L Length Overall mm	130 mm
Dimension - Length Overall inch	5.1 in
Dimension - Outside Diameter inch	0.70 in

Conductor Related

Conductor - AL Str Size	2/0 (7) AWG
Conductor - AL Str Size Range	2/0 (7) AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)