


# YCS271R

by Burndy  
Catalog ID: YCS271R

Prop 65 Notice

Al Compression Loop Splice, 159 kcmil ACSR



## Product Details

### General

Connector Type	Splice
Die Index	317
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810178850
UPC 12 Digit	7818101788500

### Dimensions

Dimension - B Length inch	4.31 in
Dimension - L Length Overall mm	224 mm
Dimension - Length Overall inch	8.80 in
Dimension - Outside Diameter inch	1.25 in

### Conductor Related

Conductor - ACSR Str Size	159 (12/7) Guinea kcmil
Conductor - ACSR Str Size Range	159 (12/7) Guinea kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)