

YCS27A

by Burndy
Catalog ID: YCS27A

Prop 65 Notice

Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION)



Product Details

General

Connector Type	Splice
Die Index	247
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810100424
UPC 12 Digit	7818101004244

Dimensions

Dimension - B Length inch	1.94 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	0.77 in

Conductor Related

Conductor - AL Str Size	3/0 (7, 19) AWG
Conductor - AL Str Size Range	3/0 (7, 19) AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)