


YCS2R

by Burndy
Catalog ID: YCS2R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 5 IN L



Product Details

General

Connector Type	Splice
Die Index	239
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014974
UPC 12 Digit	7818100149744

Dimensions

Dimension - B Length inch	2.38 in
Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.91 in
Dimension - Outside Diameter inch	0.5 in

Conductor Related

Conductor - AAAC 5005 Size	77.47 (7) kcmil
Conductor - AAAC 5005 Size Range	77.47 (7) kcmil
Conductor - AAAC 6201 Size	77.47 (7) kcmil
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)