


YCS321R

by Burndy
Catalog ID: YCS321R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 6-1/2 IN L.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeves, Pre-Filled With PENETROX Joint Compound, Die Index: 490 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U490 Die, (5), Y45 Tool, U490 Die With PT-6515 Adapter, (5), Y46 Tool, U490 Die With PUADP-1 Adapter, (5), Y48B Tool, C490 Die, (3), Y60BHU Tool, L490 Die, (3), Conductor Type: ACSR, 6201, 5005, Aluminum



Product Details

General

Application	For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors
Connector Type	Splice
Die Index	490
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810820551
UPC 12 Digit	7818108205511

Dimensions

Dimension - B Length fraction	3-18/25 in
Dimension - B Length inch	3.18 in
Dimension - L Length Overall mm	164 mm
Dimension - Length Overall inch	6.47 in
Dimension - Outside Diameter inch	1.12 in

Conductor Related

Conductor - ACSR Str Size	336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336.4 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)