

# YCS361A

by Burndy  
Catalog ID: YCS361A

Prop 65 Notice

Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION)



## Product Details

### General

Connector Type	Splice
Die Index	469
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810116692
UPC 12 Digit	7818101166922

### Dimensions

Dimension - B Length fraction	3-29/50 in
Dimension - B Length inch	3.58 in
Dimension - L Length Overall mm	185 mm
Dimension - Length Overall inch	7.28 in
Dimension - Outside Diameter inch	1.5 in

### Conductor Related

Conductor - ACSS Str Size	636 (30/7) kcmil
Conductor - ACSS Str Size Range	636 (30/7) kcmil
Conductor - AL Str Size	636 kcmil (.918)

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)