


# YCS37R

by Burndy  
Catalog ID: YCS37R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index:261.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeves, Pre-Filled With PENETROX Joint Compound, Die Index: 261 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U261 Die, (6), Y45 Tool, U261 Die With PT-6515 Adapter, (6), Y46 Tool, U261 Die With PUADP-1 Adapter, (6), Y48B Tool, C261 Die, (2), Y60BHU Tool, L261 Die, (2), Conductor Type: ACSR, 6201, 5005, Aluminum



## Product Details

### General

Application	For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors
Connector Type	Splice
Die Index	261
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810015063
UPC 12 Digit	7818100150633

### Dimensions

Dimension - B Length fraction	4-22/71 in
Dimension - B Length inch	4.31 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in

### Conductor Related

Conductor - AAAC 5005 Size	559.5 (19)
Conductor - AAAC 5005 Size Range	559.5 (19)
Conductor - AAAC 6201 Size	559.5 (19)
Conductor - AAAC 6201 Size Range	559.5 (19)
Conductor - ACSR Str Size	477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker-477.0 (30/7) Hen
Conductor - AL Str Size	556.5

Conductor - AL Str Size Range	556.5
-------------------------------	-------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)