

# YCS39

by Burndy  
Catalog ID: YCS39

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Index: 627



## Product Details

### General

Connector Type	Splice
Die Index	627
Material	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014271
UPC 12 Digit	7818100142711

### Dimensions

Dimension - A Outside Diameter inch	1.7 in
Dimension - B Length fraction	3 in
Dimension - B Length inch	3.01 in
Dimension - B Outside Diameter inch	1.7 in
Dimension - Inside Diameter inch	1.06 in
Dimension - L Length Overall mm	175 mm
Dimension - Length BB inch	3.01 in
Dimension - Length Overall inch	6.88 in

### Conductor Related

Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)