


YCS43R

by Burndy
Catalog ID: YCS43R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 10-5/8 IN L.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeves, Pre-Filled With PENETROX Joint Compound, Tools, Die Set Catalog Number, And (number Of Crimps): Y45 Tool, S292, S319 Die, (9), Y46 Tool, P292, P319 Die, (9), Y48B Tool, C292, C319 Die, (3), Y60BHU Tool, L292, L319 Die, (3), Die Index: 292 Or 319, Conductor Type: ACSR, 6201, 5005, Aluminum



Product Details

General

Application	For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors
Connector Type	Splice
Die Index	292;319
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810015087
UPC 12 Digit	7818100150877

Dimensions

Dimension - B Length fraction	5-1/4 in
Dimension - B Length inch	5.25 in
Dimension - L Length Overall mm	270 mm
Dimension - Length Overall inch	10.62 in

Conductor Related

Conductor - AAAC 5005 Size	740.8 (37) kcmil
Conductor - AAAC 5005 Size Range	740.8 (37) kcmil
Conductor - AAAC 6201 Size	740.8 (37) kcmil
Conductor - AAAC 6201 Size Range	740.8 (37) kcmil
Conductor - ACSR Str Size	605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (30/19) Teal kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	636 kcmil

Conductor - AL Str Size Range	636 kcmil
-------------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)