

YCT2626

by Burndy
Catalog ID: YCT2626

Prop 65 Notice

One-piece, copper compressions tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper, Die index:166



Product Details

General

Connector Type	Splice
Die Index	166
Die Index Run Side	166
Die Index Tap Side	166
Material	Copper
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYTEE™
UPC	781810014332

Dimensions

Dimension - B Length fraction	1-1/11 in
Dimension - B Length inch	1.09 in
Dimension - Height fraction	3-1/4
Dimension - Height inch	3.26 in
Dimension - L Length Overall mm	143 mm
Dimension - Length BB inch	1.7 in
Dimension - Length Overall inch	5.62 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Width fraction	1-7/50 in
Dimension - Width inch	0.97 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - Copper Str Run	2/0 AWG
Conductor - Copper Str Run Range	2/0 AWG
Conductor - Copper Str Tap	2/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)