



## YCU28R

by Burndy  
Catalog ID: YCU28R

Prop 65 Notice

Cast AL repair sleeve for restoring conductivity to damaged conductor, 11-7/8 IN L.

Features: For Restoring Conductivity To Damaged Conductors, Made Of Cast Aluminum, Sizes Up Through 266.8 KCMIL Are U-Shaped, For 300 KCMIL And Larger, Sleeves Are Two-Piece Interlocking Elements, Use Same Die As Equivalent Full-Tension Sleeve, Use Of PENETROX Joint Compound Required, Die Index: 249 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W249 Die, (28), Y35, Y750 Tool, U249 Die, (14), Y45 Tool, U249 Die With PT-6515 Adapter, (14), Y46 Tool, U249 Die With PUADP-1 Adapter, (14), Y48B Tool, C249 Die, (7), Y60BHU Tool, L249 Die, (7), Conductor Type: ACSR, Compressed ACSR, Compact ACSR

## Product Details

### General

Application	For ACSR and Compressed And Compact Conductors
Connector Type	Sleeve
Die Index	249
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	REPAIR SLEEVE
Type	YCU-R
UPC	781810015261
UPC 12 Digit	7818100152611

### Dimensions

Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.82 in

### Conductor Related

Conductor - ACSR Cmpt Size	4/0 AWG
Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - ACSR Str Size	159 kcmil (12/7)
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG-159 (12/7) Guinea kcmil
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)