



YDR4WG1

by Burndy
Catalog ID: YDR4WG1

Prop 65 Notice

Copper Hyreducer, # 4 Sol. (Barrel A) , #6 Sol. (Barrel B).

Die Index: 162, No of crimps: 4

Product Details

General

Application	Splice
Connector Type	Splice
Die Index	162
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	COMPRESSION TERMINAL
Trade Name	HYREDUCER™
Type	Terminal
UPC	781810014424

Dimensions

Dimension - A Outside Diameter inch	0.42 in
Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - B Outside Diameter inch	0.38 in
Dimension - L Length Overall mm	67 mm
Dimension - Length BB inch	1.25 in
Dimension - Length Overall inch	2.65 in

Conductor Related

Conductor - Copper Solid Size A	4 AWG
Conductor - Copper Solid Size A Range	4 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Solid Size B Range	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)