

YDS021RP1

by Burndy
Catalog ID: YDS021RP1

HYSPLICE



Product Details

General

Connector Type	Splice
Die Index	241
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810103746
UPC 12 Digit	7818101037466

Dimensions

Dimension - Inside Diameter inch	0.41 in
Dimension - L Length Overall mm	432 mm
Dimension - Length Overall inch	17 in
Dimension - Outside Diameter inch	0.56 in

Conductor Related

Conductor - ACSR Str Size	2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)