



YDS021R

by Burndy
Catalog ID: YDS021R

Prop 65 Notice

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor:2(7/1) Sparate

Product Details

General

Connector Type	Splice
Die Index	242;241
Die Index - Element A	242
Die Index - Element B	241
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015292
UPC 12 Digit	7818100152922

Dimensions

Dimension - Aluminum Sleeve Length inch	17 in
Dimension - Steel Sleeve Length inch	4.75 in

Conductor Related

Conductor - ACSR Cmpt Size	2 AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Str Size	2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (7/1) Sparate AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)