

# YDS1W

by Burndy  
Catalog ID: YDS1W

Prop 65 Notice

Cu Full tension sleeve, #1 Sol, 5.53"L



## Product Details

### General

Connector Type	Splice
Die Index	164
Material	Copper
Oxide Inhibitor Type	Penetrox A4
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014455

### Dimensions

Dimension - A Outside Diameter inch	0.55 in
Dimension - B Length fraction	2-16/25 in
Dimension - B Length inch	2.64 in
Dimension - B Outside Diameter inch	0.55 in
Dimension - Inside Diameter inch	0.32 in
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.53 in
Dimension - Outside Diameter inch	0.55 in

### Conductor Related

Conductor - Copper Solid Size	1 AWG
Conductor - Copper Solid Size Range	1 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)