



YDS251R

by Burndy
Catalog ID: YDS251R

Prop 65 Notice

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Product Details

General

Connector Type	Splice
Die Index	253;316
Die Index - Element A	253
Die Index - Element B	316
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810092309
UPC 12 Digit	7818100923099

Dimensions

Dimension - Aluminum Sleeve Length inch	22.25 in
Dimension - B Length fraction	2-64/79 in
Dimension - B Length inch	2.81 in
Dimension - L Length Overall mm	159 mm
Dimension - Length Overall inch	6.25 in
Dimension - Outside Diameter inch	1.14 in
Dimension - Steel Sleeve Length inch	6.25 in

Conductor Related

Conductor - ACSR Str Size	101.8 (12/7) Petrel kcmil
Conductor - ACSR Str Size Range	101.8 (12/7) Petrel kcmil
Conductor - AL Str Size	101.8 (12-7)
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	15
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)