

YDS25AT

by Burndy
Catalog ID: YDS25AT

Prop 65 Notice

Aluminium Hysplice, 7-1/4 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors, Die index: 243.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 243 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W243 Die, (6) Or BG Die, (12), Y35, Y750 Tool, BG Or U243 Die, (3), Y45 Tool, U243 Die With PT-6515 Adapter, (3), Y46 Tool, U243 Die With PUADP-1 Adapter, (3), Conductor Type: Aluminum, Compressed Aluminum, Compact Aluminum



Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Color Code	Yellow
Connector Type	Splice
Die Index	BG or 243
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810820971
UPC 12 Digit	7818108209711

Dimensions

Dimension - B Length fraction	3-53/93 in
Dimension - B Length inch	3.57 in
Dimension - L Length Overall mm	185 mm
Dimension - Length Overall inch	7.27 in
Dimension - Outside Diameter inch	0.62 in

Conductor Related

Conductor - ACSR Cmpt Size	1/0 AWG
Conductor - ACSR Cmpt Size Range	1/0 AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)