

# YDS25RLS15

by Burndy  
Catalog ID: YDS25RLS15

Prop 65 Notice

Al Compression Full Tension Splice, 1/0 Smooth Body ACSR #150 Grade



## Product Details

### General

Connector Type	Splice
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	621945135512
UPC 12 Digit	6219451355122

### Dimensions

Dimension - Inside Diameter inch	0.45 in
Dimension - L Length Overall mm	326 mm
Dimension - Length Overall inch	12.82 in
Dimension - Outside Diameter inch	0.84 in

### Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)