

YDS28AT

by Burndy
Catalog ID: YDS28AT

Prop 65 Notice

Aluminium Hysplice, 10-1/2 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 249 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W249 Die, (12), Y35, Y750 Tool, U249 Die, (6), Y45 Tool, U249 Die With PT-6515 Adapter, (6), Y46 Tool, U249 Die With PUADP-1 Adapter, (6), Y48B Tool, C249 Die, (3), Y60BHU Tool, L249 Die, (3), Conductor Type: Aluminum, Compressed Aluminum, Compact Aluminum



Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Connector Type	Splice
Die Index	249
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810821091
UPC 12 Digit	7818108210911

Dimensions

Dimension - B Length fraction	5-9/53 in
Dimension - B Length inch	5.17 in
Dimension - L Length Overall mm	266 mm
Dimension - Length Overall inch	10.47 in
Dimension - Outside Diameter inch	0.86 in

Conductor Related

Conductor - ACAR Str Size	4/0 (7) AWG
Conductor - ACAR Str Size Range	4/0 (7) AWG
Conductor - ACSR Cmpt Size	4/0 AWG
Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)