



## YDS28RE

by Burndy  
Catalog ID: YDS28RE

Prop 65 Notice

HYSPLICE ASSEMBLY

## Product Details

### General

Connector Type	Splice
Die Index - Element B	249
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810081235
UPC 12 Digit	7818100812355

### Dimensions

Dimension - B Length fraction	2-8/17 in
Dimension - B Length inch	2.47 in
Dimension - L Length Overall mm	478 mm
Dimension - Length Overall inch	18.81 in
Dimension - Outside Diameter inch	0.88 in

### Conductor Related

Conductor - ACSR Cmpt Size	4/0 AWG
Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

## Logistics

Minimum Pack Quantity	25
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)