



YDS2RLS20

by Burndy
Catalog ID: YDS2RLS20

Prop 65 Notice

Al Compression Full Tension Splice, #2 Smooth Body ACSR #200 Grade

- Made from hydrophobic silicone polymer

Product Details

General

Connector Type	Splice
Die Index	249
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	621945068124
UPC 12 Digit	6219450681244

Dimensions

Dimension - L Length Overall mm	357 mm
Dimension - Length Overall inch	14.05 in

Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)