

YDS31

by Burndy
Catalog ID: YDS31

Prop 65 Notice

Hysplice, 350 (12, 19, 37) Str., 10-1/4 in L, Full Tension Sleeve for Stranded Copper Conductors.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 267 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U267 Die, (12), Y45 Tool, U267 Die With PT-6515 Adapter, (12), Y46 Tool, U267 Die With PUADP-1 Adapter, (12), Y48B Tool, C267 Die, (4), Y60BHU Tool, L267 Die, (4), Conductor Type: Stranded Copper



Product Details

General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	267
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810821107

Dimensions

Dimension - B Length inch	5.04 in
Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.20 in
Dimension - Outside Diameter inch	1.17 in

Conductor Related

Conductor - Copper Str Size	350 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)