



YDS341RLY

by Burndy
Catalog ID: YDS341RLY

Prop 65 Notice

One piece full tension aluminum splice designed to eliminate possible basketing of conductor. Installed by crimping from end of connector towards the center.

Product Details

General

Connector Type	Splice
Die Index	327
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810100332
UPC 12 Digit	7818101003322

Dimensions

Dimension - B Length fraction	11-3/4 in
Dimension - B Length inch	11.75 in
Dimension - L Length Overall mm	602 mm
Dimension - Length Overall inch	23.71 in
Dimension - Outside Diameter inch	1.31 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee
Conductor - AL Str Size	397.5
Conductor - AL Str Size Range	397.5
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)