

# YDS34

by Burndy  
Catalog ID: YDS34

Prop 65 Notice

Hysplice, 500 (19, 37) , 11-5/8 in L, Full Tension Sleeve for Stranded.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 210 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U210 Die, (15), Y45 Tool, U210 Die With PT-6515 Adapter, (15), Y46 Tool, U210 Die With PUADP-1 Adapter, (15), Y48B Tool, C210 Die, (5), Y60BHU Tool, L210 Die, (5), Conductor Type: Stranded Copper



## Product Details

### General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	210
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	5
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810014677

### Dimensions

Dimension - B Length fraction	5-3/4 in
Dimension - B Length inch	5.75 in
Dimension - L Length Overall mm	295 mm
Dimension - Length Overall inch	11.62 in
Dimension - Outside Diameter inch	1.38 in

### Conductor Related

Conductor - Copper Str Size	500 kcmil
-----------------------------	-----------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)