



## YDS361RLY

by Burndy  
Catalog ID: YDS361RLY

Prop 65 Notice

One piece full tension aluminum splice designed to eliminate possible basketing of conductor. Installed by crimping from end of connector towards the center.

## Product Details

### General

Connector Type	Splice
Die Index	788;720
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810042267
UPC 12 Digit	7818100422677

### Dimensions

Dimension - B Length fraction	12-11/25 in
Dimension - B Length inch	12.44 in
Dimension - L Length Overall mm	635 mm
Dimension - Length Overall inch	25 in
Dimension - Outside Diameter inch	1.41 in

### Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477(18-1)kcmil
Conductor - AL Str Size Range	477 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)