



YDS36R

by Burndy
Catalog ID: YDS36R

Prop 65 Notice

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 7.88 IN L, Outer Sleeve: 26.38 IN L.

Features: Two-Piece, Full Tension HYSPLICE, Consists Of Aluminum Outer Sleeve And Steel Inner Sleeve, Tapered Outer Sleeve Provides Gradual Transition Of Stress, Filler Holes Provided For PENETROX Joint Compound, Sizes 1/0 And Larger Supplied With Plugs For Filler Hole, Installed With Standard HYSPLICE Tools And Dies (Thru 556 With Y35 Or Y750 HYPRESS), Aluminum And Steel Sleeves Can Be Ordered Separately Or In Sets, Die Index: 350 Element A, 261 Element B, Conductor Type: ACSR, Compressed, Compact, Tools, Die Set Catalog Number, And (number Of Crimps): Y35 Tool, U350 Die, (12), Y750 Tool, U261 Die, (12), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y48B Tool, C350, C261 Die, (4), Y60BHU Tool, L350, L261 Die, (4), Includes: YDS37RP1 Aluminium Sleeve And YDS36RP2 Steel Sleeve

Product Details

General

Application	For ACSR, Compressed And Compact Conductors
Connector Type	Splice
Die Index	350;261
Die Index - Element A	350
Die Index - Element B	261
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-R Set
UPC	781810015759
UPC 12 Digit	7818100157599

Dimensions

Dimension - Aluminum Sleeve Length inch	26.375 in
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.89 in
Dimension - Steel Sleeve Length inch	7.875 in

Conductor Related

Conductor - ACSR Str Size	477.0 (26/7) Hawk kcmil
Conductor - ACSR Str Size Range	477.0 (26/7) Hawk kcmil
Conductor Type	<ul style="list-style-type: none"> ACSR C Str-Size AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)