


YDS375H

by Burndy
Catalog ID: YDS375H

Prop 65 Notice

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension), Die index: 304.

Features: Full-Tension HYSPLICE Sleeves Designed For HS, EHS, Utilities (UT) Or Siemens-Martin (SM) Galvanized Steel Guy, Messenger, And Static Conductors, Made Of Hot-Dip Galvanized Seamless Milled Steel Tubing Lined With Silicone Carbide Particles, Die Index: 304 Element A, Conductor Type: Steel, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U304 Die, (12), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y48B Tool, C304 Die, (4), Y60BHU Tool, L304 Die, (4), Wire Grade: HS Or UT



Product Details

General

Application	For HS, EHS, Utilities (UT) Or Siemens-Martin (SM) Galvanized Steel Guy, Messenger, And Static Conductors
Connector Type	Splice
Die Index	304
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-H
UPC	781810016015
UPC 12 Digit	7818100160155

Dimensions

Dimension - B Length fraction	4-17/81 in
Dimension - B Length inch	4.21 in
Dimension - L Length Overall mm	230 mm
Dimension - Length Overall inch	9.07 in
Dimension - Outside Diameter inch	0.75 in

Conductor Related

Conductor - AL Coated Steel Size	3/8 (7) in
Conductor - AL Coated Steel Size Range	3/8 (7) in
Conductor - Galvanized Steel Str Size	3/8 (7) in
Conductor - Galvanized Steel Str Size Range	3/8 (7) in
Conductor - Grade	HS, UT
Conductor Type	<ul style="list-style-type: none"> ACSR C Str-Size AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)