

YDS391AT

by Burndy
Catalog ID: YDS391AT

Prop 65 Notice

Hysplice, 13-5/8 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Tools, Die Set Catalog Number, And (number Of Crimps): Y45 Tool, S342 Die, (8), Y46 Tool, P342 Die, (8), Y48B Tool, C342 Die, (4), Y60BHU Tool, L342 Die, (4), Die Index: 342 Element A, Conductor Type: Aluminum, Compressed Aluminum, Compact Aluminum



Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Connector Type	Splice
Die Index	342
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810821169
UPC 12 Digit	7818108211699

Dimensions

Dimension - B Length fraction	6-18/25 in
Dimension - B Length inch	6.72 in
Dimension - L Length Overall mm	344 mm
Dimension - Length Overall inch	13.56 in
Dimension - Outside Diameter inch	1.67 in

Conductor Related

Conductor - ACSR Str Size	795 (30/19) Mallard kcmil
Conductor - ACSR Str Size Range	795 (30/19) Mallard kcmil
Conductor - AL Str Size	800 kcmil
Conductor - AL Str Size Range	800 kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)