



## YDS392R

by Burndy  
Catalog ID: YDS392R

Prop 65 Notice

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

## Product Details

### General

Connector Type	Splice
Die Index	305;608
Die Index - Element A	305
Die Index - Element B	608
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810109007
UPC 12 Digit	7818101090077

### Dimensions

Dimension - Aluminum Sleeve Length inch	26.125 in
Dimension - L Length Overall mm	664 mm
Dimension - Length Overall inch	26.13 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Steel Sleeve Length inch	8.625 in

### Conductor Related

Conductor - ACSR Str Size	556.5 (24/7) Parakeet;556.5 (26/7) Dove
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet-556.5 (26/7) Dove
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)