



YDS39R44RS

by Burndy
Catalog ID: YDS39R44RS

Prop 65 Notice

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Product Details

General

Connector Type	Splice
Die Index	608;225
Die Index - Element A	225
Die Index - Element B	608
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810095492
UPC 12 Digit	7818100954922

Dimensions

Dimension - Aluminum Sleeve Length inch	32.50 in
Dimension - L Length Overall mm	663.7 mm
Dimension - Length Overall inch	26.13 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Steel Sleeve Length inch	8 in

Conductor Related

Conductor - ACSR Str Size	556.5 (24/7) Parakeet;556.5 (26/7) Dove
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet-556.5 (26/7) Dove
Conductor - AL Str Size	556.5
Conductor - AL Str Size Range	556.5
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)