

YDS39

by Burndy
Catalog ID: YDS39

Prop 65 Notice

Cu Tube Compression Single Sleeve Full Tension Splice, 750 Kcmil Cu Cable(37.61 Str.), 12.78" L, 627 Index



Product Details

General

Connector Type	Splice
Die Index	627
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	7
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810821121

Dimensions

Dimension - B Length fraction	6-1/100in
Dimension - B Length inch	6.01 in
Dimension - L Length Overall mm	325 mm
Dimension - Length Overall inch	12.78 in
Dimension - Outside Diameter inch	1.70 in

Conductor Related

Conductor - Copper Str Size	750 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)