

YDS44

by Burndy
Catalog ID: YDS44

Prop 65 Notice

Cu Tube Compression Single Sleeve Full Tension Splice, 1000 Kcmil Cu Cable(37.61 Str.), 15.25" L, 345 Index



Product Details

General

Connector Type	Splice
Die Index	345
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	10
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014684

Dimensions

Dimension - B Length fraction	1-14/25 in
Dimension - B Length inch	7.56 in
Dimension - L Length Overall mm	387 mm
Dimension - Length Overall inch	15.25 in
Dimension - Outside Diameter inch	2.00 in

Conductor Related

Conductor - Copper Str Size	1000 kcmil
-----------------------------	------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)