



YDS49R36RS

by Burndy
Catalog ID: YDS49R36RS

Prop 65 Notice

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Product Details

General

Connector Type	Splice
Die Index	422
Die Index - Element A	350
Die Index - Element B	422
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810129371

Dimensions

Dimension - Aluminum Sleeve Length inch	37 in
Dimension - L Length Overall mm	941 mm
Dimension - Length Overall inch	37.03 in
Dimension - Outside Diameter inch	2.12 in
Dimension - Steel Sleeve Length inch	7.857 in

Conductor Related

Conductor - ACSR Str Size	1033.5 (54/7) Curlew
Conductor - ACSR Str Size Range	1033.5 (54/7) Curlew
Conductor - AL Str Size	1033.5
Conductor - AL Str Size Range	1033.5
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)