

YDS4CA

by Burndy
Catalog ID: YDS4CA



Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Die Index: 162, 2-5/8 L.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Holding Strength: Aluminum: 700 LB, Die Index: 162, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W162 Die, (4), Y35, Y750 Tool, U162 Die, (1), Y45 Tool, U162 Die With PT-6515 Adapter, (1), Y46 Tool, U162 Die With PUADP-1 Adapter, (1), Conductor Type: Aluminum, Color Code: Orange

Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Color Code	Orange
Connector Type	Splice
Die Index	162
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-A
UPC	781810015377

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Inside Diameter inch	0.24 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Outside Diameter inch	0.4 in

Conductor Related

Conductor - AAAC 5005 Size	48.69 (7) kcmil
Conductor - AAAC 5005 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size	48.69 (7) kcmil
Conductor - AAAC 6201 Size Range	48.69 (7) kcmil
Conductor - ACAR Str Size	4 (7) AWG
Conductor - ACAR Str Size Range	4 (7) AWG
Conductor - ACSR Cmpt Size	4 AWG

Conductor - ACSR Cmpt Size Range	4 AWG
Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)