



YDS4RLS20

by Burndy
Catalog ID: YDS4RLS20

Prop 65 Notice

Al Compression Full Tension Splice, #4 Smooth Body ACSR #200 Grade

Product Details

General

Connector Type	Splice
Die Index	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	621945068636

Dimensions

Dimension - B Length fraction	5-32/33 in
Dimension - B Length inch	5.97 in
Dimension - Inside Diameter inch	0.31 in
Dimension - L Length Overall mm	306 mm
Dimension - Length Overall inch	12.05 in
Dimension - Outside Diameter inch	0.69 in

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG
Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)