



YDS6RLS20CG1

by Burndy
Catalog ID: YDS6RLS20CG1

Prop 65 Notice

Single sleeve aluminum UNISPLICE; Full tension aluminum and ACSR applications; prefilled with PENETROX joint compound

Product Details

General

Connector Type	Splice
Die Index	165
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	621945068759

Dimensions

Dimension - B Length fraction	5-22/25 in
Dimension - B Length inch	5.88 in
Dimension - Inside Diameter inch	0.28 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)