

# YDS7K7

by Burndy  
Catalog ID: YDS7K7

Prop 65 Notice

Full tension copper splice designed to exceed the rated breaking strength of 30 percentage high conductivity EHS copperweld and lower strength conductors, Die Index: 328



## Product Details

### General

Connector Type	Splice
Die Index	328
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014608

### Dimensions

Dimension - B Length inch	2.79 in
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.20 in
Dimension - Outside Diameter inch	1.11 in

### Conductor Related

Conductor - CopperWeld Str Size	2/0 F AWG
---------------------------------	-----------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)